

CLESSENCE Advanced Toilet Seat



# Enjoy the proven benefits of the **CLESSENCE** Advanced Toilet Seat

The INAX **CLESSENCE** Advanced Toilet Seat is a stylish, compact accessory that enhances the look of your bathroom and, most importantly, lets you take control of the personal moments of your daily life.

The **CLESSENCE** Advanced Toilet Seat provides the ultimate in personal cleansing and bathroom luxury, whether retrofitted to your existing toilet or specified in the bathroom of your new home, business, or public facility. Our ultramodern design incorporates sophisticated functions and superior ease of use, allowing anyone to experience the benefits of bidet cleansing at the touch of a button.

## Hygiene

With the **CLESSENCE** Advanced Toilet Seat you and your family can bring the highest standards of cleanliness and convenience to everyday personal care.

Our spray units combine advanced technological features such as sensitive temperature and water pressure controls to ensure thorough cleansing for both posterior and feminine washing, all with a level of freshness and comfort that makes hygienic care easy and pleasant for children and adults alike. There is no better way to maintain a higher standard of personal care.

## Comfort

The **CLESSENCE** Advanced Toilet Seat provides a new standard of bathroom comfort for men and women of all ages. From start to finish, we have designed the entire washing experience to be as simple, effective, and refreshing as possible. You'll notice the difference from the moment you sit on the heated seat—a warm welcome instead of a mid-winter wake-up. And after using the toilet, a simple touch of a button of the flat-design controller activates a warm water spray that cleans and soothes.

## Independence

Being free from worry about intimate hygiene is part of aging gracefully. The ability to independently carry out daily personal care can be a great source of self-assurance and relief for the medically or physically impaired.

The **CLESSENCE** Advanced Toilet Seat allows people with physical or other difficulties to attend to intimate hygiene with dignity and independence, confident that the advanced design and proven features will get them clean and comfortable—every time.



# Proven Reliability

## Advanced Toilet Seat

### Made by **INAX**

## Functionality

### Posterior Wash



The three-jet posterior wash nozzle arm directs a cleansing stream of warm water nearly vertically, for effective posterior cleaning after using the toilet.



### Feminine Wash



The feminine wash operates from a separate bidet nozzle that projects a softer, ten-jet spray of warm water upwards and forwards, for gentle rinsing of feminine areas.



### Nozzle Cleaning



The nozzle cleaning function automatically cleans nozzles after each use.



### Warm Water



The water heating system incorporates many safety features, including a thermostat sensor, a thermal fuse, and a high temperature cut-off switch to prevent overheated water being sprayed.

### Control Panel



Operation of the functions is as simple as a touch of a button. The flat design also makes cleaning easy.



### Heated Toilet Seat



The low-wattage heated toilet seat is built to the strictest safety standards, for years of trouble-free use and peace of mind.



### Dryer



The dryer supplies warm, drying air after use of the water sprays, and can be preceded by light use of toilet tissue. Air drying reduces irritation and discomfort from toilet tissue.

### Occupied Seat Sensor



This safety feature prevents the unexpected activation of the spray functions by locking the water control switches if the seat is unoccupied.



### One-touch Installation



Installation is easy as click and attach. Simply reverse the process to release the unit for easy cleaning.



### Energy Saver



By activating the energy saver function, the unit switches off for 6 hours, conserving energy and running costs when not in use.

### Slow-Down Toilet Seat and Lid




This convenient unidirectional feature slowly lowers the toilet lid and seat to prevent them from banging shut when released, yet allows both to be freely opened.

# CLESSENCE Specifications


TYPE	CW-H230-US (Round)	CW-H231-US (Elongated)
Water Supply Method	Direct connection to tap water	
Tap Water Pressure Range	8.5-106.7 psi (0.06-0.74 Mpa)	
Maximum Rating	AC120V,297W,60Hz	
Dimensions	19.3"W x20.7"D x5.9"H	19.3"W x21.5"D x5.9"H
Weight	9.9 lbs.	
POSTERIOR, BIDET CLEANSING	Warm Water Tank Capacity	0.26 gal.
	Nozzles	Auto slide type: exclusively posterior and bidet
	Cleaning Spray Volume	0~0.24 gal./min
	Warm Water Heater Capacity	250W
	Warm Water Temperature	Four steps selectable / Off (tap water temperature), Low (94°F), Medium (100°F), High (103°F)
DRYING	Air Volume	105.9 ft. <sup>3</sup> /min
	Warm Air Heater Capacity	0, 65, 130 W
	Warm Air Temperature	Three steps selectable / Low (room temp.), Medium, High
TOILET SEAT	Heater Capacity	45W
	Surface Temperature	Four steps selectable / Off (room temperature), Low (87°F), Medium (93°F), High (99°F)
Power Cord	3.3 ft.	
Other Functions	<ul style="list-style-type: none"> <li>•Occupied seat sensor</li> <li>•Toilet seat and toilet seat lid Slow-Down</li> <li>•Toilet seat heater auto shut-off</li> <li>•Main body detachment</li> <li>•Power saving function</li> <li>•Power button (2 second press upon [STOP] button)</li> <li>•Nozzle auto cleaning</li> </ul>	

## Simple, one-touch installation


The CLESSENCE Advanced Toilet Seat is compatible with standard U.S. toilets, and can easily be installed on the majority of existing toilet units. Installation is unlikely to take more than 30 minutes. Detailed instructions are provided in materials accompanying your new CLESSENCE Advanced Toilet Seat. If you prefer professional installation, please consult your dealer.



1. Install the junction valve to the water supply.



2. Install the seat body.



3. Connect the water supply.



『Contact US』

**MONITOR PRODUCTS, INC.**

P.O. Box 3408  
 Princeton, NJ 08543  
 Phone Toll Free: (800) 524-1102  
 Phone in New Jersey: (732) 329-0900  
 Fax: (732) 329-0904  
[www.monitorproducts.com](http://www.monitorproducts.com)